

CIG BUMP CAP

100% cotton ball cap with padded insert

Protects against lacerations, minor bumps and bruises in areas that do not require certified safety helmets



- > Hook & loop size adjustment
- > Embroidery available
- > Vent holes for breathability
- > Ideal for meat packing, food/beverage processing, warehousing, auto repair, pest control and home inspection
- > Shell not interchangeable with any other ball cap
- > Cap weight: 5.7 oz
- > Not a hard hat

HOW TO USE

To ensure effective protection, this shock-proof cap must be worn with its visor facing to the front and should be adjusted to the user's head size using the fastener located at the rear of the cap (adjustable from 55/58 cm to 62 cm head circumference)

While the bump cap is free from defects it is suitable for its intended purpose.

Under normal circumstances the bump cap should offer adequate protection for 2 to 3 years (after first use) or 5 years according to the manufacturing date.

The bump cap's useful life is affected by many factors including the cold, heat, chemicals, sunlight and misuse. The bump cap should be examined daily or obvious signs of cracking, brittleness or damage.

Do not apply paint, solvents, adhesives or self-adhesive labels, except in accordance with instructions from the bump cap manufacturer.

INSTRUCTION FOR SORAGE

When not in use or during transportation the bump cap should be stored in a container such that it is out of direct sunlight and not in contact with any chemicals, liquids or sharp objects and will not become deformed by objects dropping on to it. It is not necessary to put the cap in a bag.
aliquam erat

INSTRUCTION FOR CLEANING

The bump cap should be cleaned / disinfected by wiping with a cloth moistened with a weak mild detergent solution, the cap should then be allowed to air dry. No strong or abrasive chemicals should be used. If the bump cap can not be cleaned by this method it should be replaced.

